



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL2630 LKG RCPT, 30A 277V, 2P3W, L7-30R, BK** *Hubbell Wiring Devices*

Catalog Number	HBL2630
Manufacturer	Hubbell Wiring Devices
Description	Twist-Lock® Industrial Flush Receptacle, 30A 277V Ac, 2-Pole 3-Wire Grounding, L7, Screw Terminal
Weight per unit	0.2500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### **Features**

amperage rating	30
connection	Screw Terminal
Current Rating	30
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	3-Wire
pallet quantity	2520
Phase	1
Poles	2-Pole
Voltage Rating	277 VAC
Wattage	8,310
Wire Size	#16 to #8

### **Dimensions and Weight**

Size	3.28 in x 1.70 in x 1.31 in
------	-----------------------------

### **Descriptions**

Description	LKG RCPT, 30A 277V, 2P3W, L7-30R, BK
extra long description	HWDK HBL2630 LKG RCPT, 30A 277V, 2P
Long Description	Twist-Lock® Industrial Flush Receptacle, 30A 277V AC, 2-Pole 3-Wire Grounding, L7, Screw Terminal
Product Type	LKG RCPT, 30A 277V, 2P3W, L7-30R, BK
Special Features	Standard

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585236056
Manufacturers Part Number	HBL2630
UPC	783585236056

### **Taxonomies, Classifications, and Categories**

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Single Flush Receptacle



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.25

## Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	L7-30R
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498