



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBL2715SW LKG WT S/SHD FL-Inlt, 30A125/250V, L14-30P

Hubbell Wiring Devices

Catalog Number	HBL2715SW
Manufacturer	Hubbell Wiring Devices
Description	Watertight Safety-Shroud®, Locking Devices, Twist-Lock®, Flanged Inlet, 30A 125/250V Ac, 3-Pole 4-Wire Grounding, Nema L14- 30P, Screw Terminal, Gray.
Weight per unit	0.3010 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	30
connection	Screw Terminals
Current Rating	30
Dielectric Strength	Withstands 2,000V minimum
insulation	True
Number of Wires	4-Wire
pallet quantity	950
Phase	1
Poles	3-Pole
Voltage Rating	125/250 V
Wattage	7,500
Wire Size	#16 to #8

### Dimensions and Weight

Size	3.75 in x 3.75 in x 2.44 in
------	-----------------------------

### Descriptions

Description	LKG WT S/SHD FL-INLT,30A125/250V,L14-30P
extra long description	HWDK HBL2715SW LKG WT S/SHD FL-INLT
Long Description	Watertight Safety-Shroud®, Locking Devices, Twist-Lock®, Flanged Inlet, 30A 125/250V AC, 3-Pole 4-Wire Grounding, NEMA L14- 30P, Screw Terminal, Gray.
Product Type	LKG WT S/SHD FL-Inlt, 30A125/250V, L14-30P
Special Features	Shrouded Watertight Construction

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585231808
Manufacturers Part Number	HBL2715SW
UPC	783585231808



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Flanged Inlet

## Packaging

Carton	1
Package	5
Weight Per each	0.301

## Uses, Certifications, and Standards

Application	Extra Heavy Duty Industrial
environmental conditions	Watertight
Mounting	Screw Mount
nema rating	L14-30P
standard	UL Listed, CSA Certified To Type 4, 4X And Type 12