



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL4710ST LKG SGL RCPT, 15A 125V, L5-15R, BK, ST *Hubbell Wiring Devices*

Catalog Number	HBL4710ST
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Edgeconnect™ Twist-Lock®, Industrial, Flush Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screwless Terminal, Black
Weight per unit	0.1500 (lbs/each)
Product Category	Wiring Devices

Features

connection	EdgeConnect™ Screwless Termination
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	3
Phase	1
Poles	2
Voltage Rating	15 VAC

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Size	Standard Sized Product
------	------------------------

Descriptions

Description	LKG SGL RCPT, 15A 125V, L5-15R, BK, ST
extra long description	HWDK HBL4710ST LKG SGL RCPT, 15A 12
Features	EdgeConnect™ Screwless Termination system, simply insert the wire and press the plunger down. No tools are required. That connection is fool-proof and long lasting, to all but guarantee a high quality result. Any qualified installer regardless of level of training can guarantee a high quality result.
Long Description	Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Flush Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screwless Terminal, Black
Product Type	LKG SGL RCPT, 15A 125V, L5-15R, BK, ST
Special Features	EdgeConnect™ Technology, Screwless Termination

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585719634
Manufacturers Part Number	HBL4710ST
series	EdgeConnect™
UPC	783585719634



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	RECEPTACLE

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Package	10
Weight Per each	0.15

Uses, Certifications, and Standards

Application	Industrial
environmental conditions	IP20 Suitability
Mounting	Screw Mount
nema rating	L5-15R
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498
Temperature Rating	Maximum Continuous 75°C, Minimum -40°C (w/o impact)