



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1461 Technology Pkwy  
30165-0000, GA Rome  
Phone: 706-622-4953  
Fax: 706-622-4954



## HBL4750 LKG Dup RCPT, 15A 277V, L7-15R, BR *Hubbell Wiring Devices*

Catalog Number	HBL4750
Manufacturer	Hubbell Wiring Devices
Description	Twist-Lock® Industrial Duplex Flush Receptacle, 15A 277V Ac, 2-Pole 3-Wire Grounding, Nema L7-15R, Screw Terminal
Weight per unit	0.0650 (lbs/each)
Product Category	Metallic Raceway & Accessories

### Features

amperage rating	15
connection	Screw Terminal
Current Rating	15
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
pallet quantity	5500
Phase	1
Poles	2-Pole
Voltage Rating	277 VAC
Wattage	4,155
Wire Size	#18 to #10

### Dimensions and Weight

Size	3.29 in x 1.70 in x 1.17 in
------	-----------------------------

### Descriptions

Description	LKG DUP RCPT, 15A 277V, L7-15R, BR
extra long description	HWDK HBL4750 LKG DUP RCPT, 15A 277V
Long Description	Twist-Lock® Industrial Duplex Flush Receptacle, 15A 277V AC, 2-Pole 3-Wire Grounding, NEMA L7-15R, Screw Terminal
Product Type	LKG Dup RCPT, 15A 277V, L7-15R, BR
Special Features	Self Grounding

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585002347
Manufacturers Part Number	HBL4750
UPC	783585002347

### Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	RECEPTACLE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1461 Technology Pkwy  
30165-0000, GA Rome  
Phone: 706-622-4953  
Fax: 706-622-4954

## Packaging

Carton	1
Package	10
Weight Per each	0.065

## Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	L7-15R
standard	Certified to CSA C22.2 No.42;Fed. Spec. W-C-596;Listed to UL 498;WR Rating