



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBL5661 SGL RCPT, Ind GRD, 15A 250V, 6-15R, BR *Hubbell Wiring Devices*

Catalog Number	HBL5661
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Single, Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown, Single Pack
Weight per unit	0.1500 (lbs/each)
Product Category	Wall Plates & Covers

### Features

amperage rating	15
connection	Back and Side Wired
Current Rating	15
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
pallet quantity	5500
Phase	1
Poles	2-Pole
Voltage Rating	250 V
Wattage	3,750
Wire Size	#12 to #10

### Dimensions and Weight

Size	1.94 in x 1.63 in x 1.19 in
------	-----------------------------

### Descriptions

Description	SGL RCPT, IND GRD, 15A 250V, 6-15R, BR
extra long description	HWDK HBL5661 SGL RCPT, IND GRD, 15A
Long Description	Straight Blade Devices, Receptacles, Single, Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown, Single Pack
Product Type	SGL RCPT, Ind GRD, 15A 250V, 6-15R, BR
Special Features	Standard

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585013992
Manufacturers Part Number	HBL5661
series	Extra Heavy Duty
UPC	783585013992

### Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	SINGLE RECEPTACLE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.15

## Uses, Certifications, and Standards

Application	Extra Heavy Duty
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	6-15R
standard	Certified to CSA 22.2, No. 42 File 285;Guide RTRT Fed Spec WC596G;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186