



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL8410 SGL RCPT, 3P4W, 20A 125/250V, 14-20R, BK Hubbell Wiring Devices

Catalog Number	HBL8410
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Flush Receptacle, Industrial Grade, 3-Pole 4-Wire Grounding, 20A 125/250V, 14-20R, Black, Single Pack.
Weight per unit	0.2500 (lbs/each)
Product Category	Wall Plates & Covers

Features

amperage rating	20
connection	Back and Side Wired Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	4-Wire
Phase	1
Poles	3-Pole
Voltage Rating	125/250 V
Wattage	5000
Wire Size	#14 to #10

Dimensions and Weight

Size	2.44 in x 1.5 in x 1.24 in
------	----------------------------

Descriptions

Description	SGL RCPT, 3P4W, 20A 125/250V,14-20R,BK
extra long description	HWDK HBL8410 SGL RCPT, 3P4W, 20A 12
Long Description	Straight Blade Devices, Receptacles, Flush Receptacle, Industrial Grade, 3-Pole 4-Wire Grounding, 20A 125/250V, 14-20R, Black, Single Pack.
Product Type	SGL RCPT, 3P4W, 20A 125/250V, 14-20R, BK
Special Features	Self Grounding

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585015705
Manufacturers Part Number	HBL8410
series	Extra Heavy Duty
UPC	783585015705

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	RECEPTACLE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.25

Uses, Certifications, and Standards

Application	Extra Heavy Duty Hospital Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	14-20R
standard	CSA Certified to C22.2 No. 42 File 280C;NEMA® WD-6 Compliant;UL Listed to UL498 File E1706