



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HF1016414 10", 115V S-MT FLTR Fan

Hoffman Enclosures, Inc.

Catalog Number	HF1016414
Manufacturer	Hoffman Enclosures, Inc.
Description	HF10 Side-Mount Filter Fan, 115V 159CFM, LT Gray
Weight per unit	3.1 (lbs/each)
Product Category	20160927104906

Features

Ambient Temperature	14 to 131 deg F
amperage rating	0.38/0.36 A
flow rate	159 CFM
Material	Plastic
nominal voltage	115
Voltage Rating	115 VAC

Material, Color, and Finish

Color	Light Gray
Color Code	RAL 7035
Finish	Smooth Matte
Housing Material	Non-metallic

Dimensions and Weight

Size	10.13 x 10.14 x 4.68 in
------	-------------------------

Descriptions

Description	10", 115V S-MT FLTR FAN
extra long description	NVENT HOF HF1016414 IP54 10 in FF 1
Features	HF Side-Mount Filter Fans quickly install into enclosure with a click-fit design; no tools or screws required. Grilles open with the flick of a finger for easy filter replacement.
Long Description	HF10 Side-Mount Filter Fan, 115V 159CFM, Lt Gray
Product Type	IP54 10 In FF 115V 7035

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510342036
Manufacturers Part Number	HF1016414
UPC	783510342036

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	Fans and Filter Fans



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	3.09

Uses, Certifications, and Standards

Application	Power Distribution; Controls and Drives
-------------	---