



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HFD3015 Type HFD 3P 15A Trip 600V Class 65KA At 480V No

Eaton Corp

Catalog Number	HFD3015
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, HFD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Three-Pole, 15 A, 600 Vac, 250 VDC, Load Side, 50/60 HZ
Weight per unit	4.3 (lbs/each)
Product Category	3 Pole

### Features

Current Rating	15 A
dimensions	3.3800 IN X 4.1300 IN X 6.0000 IN
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	600 VAC, 250 VDC

### Descriptions

Description	TYPE HFD 3P 15A TRIP 600V CLASS 65KA AT 480V NO
extra long description	ETN HFD3015 HFD 3P 15A
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, HFD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 15 A, 600 Vac, 250 Vdc, Load side, 50/60 Hz
Product Type	HFD 3P 15a

### Manufacturer Information

Brand	Eaton
GTIN	00786679175835
Manufacturers Part Number	HFD3015
UPC	786679175835

### Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	4.25

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
Frequency Rating	50/60 Hz
standard	UL Listed