



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HLCMS9129301EWH 9" 18W Led Disc Light 30K W/Motion Sensor 1200LM

Cooper Lighting Solutions

Catalog Number	HLCMS9129301EWH
Manufacturer	Cooper Lighting Solutions
Description	9-Inch Motion Sensor, Led Surface Light, 1200 Lumens, 90, 3000K, 120V, Matte White Flange Finish
Weight per unit	0.9100 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.15 (at 120V)
Lamp Type	LED
Socket Type	N/A
Voltage Rating	120V
Wattage	17.6 W

Material, Color, and Finish

Finish	Matte White, White Flange
Style	(blank)

Descriptions

Description	9" 18W LED DISC LIGHT 30K W/MOTION SENSOR 1200LM
extra long description	CLS HLCMS9129301EWH HLC W/MOTION, 9
Long Description	9-Inch Motion Sensor, LED surface light, 1200 lumens, 90, 3000K, 120V, Matte white flange finish
Product Type	HLC W/Motion, 9IN, 12LM, 3K, Single
Special Features	Low-profile lens surface-mount luminaire, Ceiling/wall mounting

Manufacturer Information

Brand	HALO
GTIN	00080083127993
Manufacturers Part Number	HLCMS9129301EWH
UPC	080083127993

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	HLC LED

Packaging

Carton	1
Package	4
Weight Per each	0.91



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting standard	Surface Mount Energy Star Certified;IECC Compliant;Title 24 Compliant;UL Certified - Damp Location;RoHS Compliant;AIR-TITE (TM) Certified ASTM E283;Damp Locations Listed;LM79/LM80 Compliant;EMI/RFI per FCC 47CFR Part 15 B;California Title 24;NEC;Title 20 Compliant