



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HLS4079301EWH12B 4" 12W Led Disk Light 30K 90CRI 120V 750LM 12 Pack *Cooper Lighting Solutions*

Catalog Number	HLS4079301EWH12B
Manufacturer	Cooper Lighting Solutions
Description	4" Led Surface Light, 700 Lumens (Nominal), 90 Cri Minimum, 3000K CCT, 120V 60HZ, Le and Te Phase, Matte White Flange Cut 10 Percent Dimming, Qty 12 Bulk Pack (Not For Individual Sale)
Weight per unit	5.8 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.101A
Lamp Type	LED
Voltage Rating	120V
Wattage	12.2 W

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	4" 12W LED DISK LIGHT 30K 90CRI 120V 750LM 12 PACK
extra long description	CLS HLS4079301EWH-12BP HLS, 4IN, 75
Long Description	4" LED surface light, 700 lumens (nominal), 90 CRI minimum, 3000K CCT, 120V 60Hz, LE and TE phase, matte white flange cut 10 percent dimming, Qty 12 bulk pack (not for individual sale)
Product Type	HLS, 4IN, 750LM, 3000K, Wet, 12PK
Special Features	Sizes include 4", 6", & 9"

Manufacturer Information

Brand	HALO
GTIN	00080083256723
Manufacturers Part Number	HLS4079301EWH-12BP
UPC	080083256723

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	HLS Round LED Surface Mount

Packaging

Carton	1
Weight Per each	5.81



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting	Surface Mount
standard	Energy Star;IECC Compliant;UL Listed;Title 24 Compliant;RoHS Compliant