

# Specifications

## Eaton HMCPE003A0C

Eaton molded case circuit breaker accessory motor protection, Motor circuit protector, 3 A, Three-pole, 480 V, Adjustable, Frame J-K, 9-30 A, 600 Y/347 V, Series G, Non-aluminum

### General specifications

<b>PRODUCT NAME</b>	Eaton molded case circuit breaker accessory motor protection
<b>CATALOG NUMBER</b>	HMCPE003A0C
<b>UPC</b>	786679113639
<b>PRODUCT LENGTH/DEPTH</b>	6.5 in
<b>PRODUCT HEIGHT</b>	5.5 in
<b>PRODUCT WIDTH</b>	3 in
<b>PRODUCT WEIGHT</b>	3 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	CSA Certified UL Listed
<b>GLOBAL CATALOG</b>	HMCPE003A0C
<b>PRODUCT TYPE</b>	Molded case circuit breaker accessory



Powering Business Worldwide

## Product specifications

<b>AMPERAGE RATING</b>	3 A
<b>VOLTAGE RATING</b>	480 V
<b>TRIP TYPE</b>	T98
<b>FRAME SIZE</b>	Frame J-K
<b>MAGNETIC TRIP RANGE</b>	9-30 A
<b>VOLTAGE - MAX</b>	600 Y/347 V
<b>SERIES</b>	Series G
<b>TERMINAL MATERIAL</b>	Non-aluminum
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Motor circuit protector

## Resources

### APPLICATION NOTES

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Current limiting molded case circuit breaker module product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Series G MCCB quick selector](#)

[StrandAble terminals product aid](#)

[Comprehensive circuit protection for control panel applications](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Motor protection circuit breakers product aid](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Breaker service centers](#)

### BROCHURES

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

### CATALOGS

### MULTIMEDIA

[Flex shaft handle installation tutorial](#)

### SPECIFICATIONS AND DATASHEETS

[MOEM MCCB product selection guide](#)

---

[NG and ND-Frame molded case circuit breakers](#)

[Eaton Specification Sheet - HMCPE003AOC](#)

---

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton HMCPE003A0C

Eaton molded case circuit breaker accessory motor protection, Motor circuit protector, 3 A, Three-pole, 480 V, Adjustable, Frame J-K, 9-30 A, 600 Y/347 V, Series G, Non-aluminum

### General specifications

<b>PRODUCT NAME</b>	Eaton molded case circuit breaker accessory motor protection
<b>CATALOG NUMBER</b>	HMCPE003A0C
<b>UPC</b>	786679113639
<b>PRODUCT LENGTH/DEPTH</b>	6.5 in
<b>PRODUCT HEIGHT</b>	5.5 in
<b>PRODUCT WIDTH</b>	3 in
<b>PRODUCT WEIGHT</b>	3 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	CSA Certified UL Listed
<b>GLOBAL CATALOG</b>	HMCPE003A0C
<b>PRODUCT TYPE</b>	Molded case circuit breaker accessory



Powering Business Worldwide

## Product specifications

<b>AMPERAGE RATING</b>	3 A
<b>VOLTAGE RATING</b>	480 V
<b>TRIP TYPE</b>	T98
<b>FRAME SIZE</b>	Frame J-K
<b>MAGNETIC TRIP RANGE</b>	9-30 A
<b>VOLTAGE - MAX</b>	600 Y/347 V
<b>SERIES</b>	Series G
<b>TERMINAL MATERIAL</b>	Non-aluminum
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Motor circuit protector

## Resources

### APPLICATION NOTES

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Current limiting molded case circuit breaker module product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Series G MCCB quick selector](#)

[StrandAble terminals product aid](#)

[Comprehensive circuit protection for control panel applications](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Motor protection circuit breakers product aid](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Breaker service centers](#)

### BROCHURES

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

### CATALOGS

### MULTIMEDIA

[Flex shaft handle installation tutorial](#)

### SPECIFICATIONS AND DATASHEETS

[MOEM MCCB product selection guide](#)

---

[NG and ND-Frame molded case circuit breakers](#)

[Eaton Specification Sheet - HMCPE003AOC](#)

---

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

