

Eaton HPC40SHL

Catalog Number: HPC40SHL

Eaton Cutler-Hammer series Housing panel, 400A, 120/240V, BRH/BWH Secondary Circuit, Aluminum Bus Material, Lever bypass, NEMA 3R Enclosure, 22 kAIC Interrupt Rating, Surface mounting, Ringless Security Circuit, 1 Socket



General specifications

Product Name	Catalog Number
Eaton house panel	HPC40SHL
UPC	Product Length/Depth
782116883837	7.75 in
Product Height	Product Width
46 in	33 in
Product Weight	Warranty
82 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

House panel

Utility approvals

NC : Dominion

VA : Dominion

OH : Dayton Power and Light (DP&L)

ID : Idaho Power

OR : Idaho Power

AK : Anchorage Municipal Light & Power

NV : NV Energy

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : Indiana Michigan Power (IMP) (AEP East)

MI : Indiana Michigan Power (IMP) (AEP East)

OH : AEP Ohio (AEP East)

TN : Appalachian Power (AEP East)

VA : Appalachian Power (AEP East)

WV : Appalachian Power (AEP East)

Interrupt rating

22 kAIC

Enclosure

NEMA 3R

Secondary circuit breaker

BRH/BWH

Amperage Rating

400 A

Line

Lug landings for compression, lugs not included

Mounting

Surface

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - 400A METER BREAKER HPC30SHL, HPC40SHL, HPC4046SHLG, HPC4046SHLGX

Specifications and datasheets

Eaton Specification Sheet - HPC40SHL

Security

Ringless

Voltage rating

120/240 V

Number of sockets

1

Used with

Type BR breakers

Bypass

Lever

Bus material

Aluminum

Feed type

Top/bottom

Main circuit breaker

CSR2200



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia