



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HR175DX39 175W ED28 Mercury Vapor White Mogul Base Lamp

*Ge By Current Lamps*

Catalog Number	HR175DX39
Manufacturer	Ge By Current Lamps
Description	Hid Mercury Vapor Lamp, 50, 3900 K, 7800 LM Brightness (Lumens), 175 W, 318 V, White, Hard Glass Material, 20000 H Average Life, Mogul Screw Base, H39 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Length, 30.3 % Mercury Content, 0.53 LB
Weight per unit	0.5300 (lbs/each)
Product Category	Hid Mercury Vapor Lamps

### Features

Base	E39
lumens	7800.0
Wattage	175.0

### Material, Color, and Finish

Color	Delux white
color rendering index (cri)	50.0
Style	Open or enclosed fixtures

### Descriptions

Description	175W ED28 MERCURY VAPOR WHITE MOGUL BASE LAMP
extra long description	GEL HR175DX39 24062 MERCURY
Special Features	8.25IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168240628
UPC	043168240628

### Taxonomies, Classifications, and Categories

Category Description	MERCURY VAPOR
----------------------	---------------

### Packaging

Carton	1
Package	12
Weight Per each	0.53

### Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------