



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HSTT1248Q2 HT Shrink Tubing *Panduit Corporation*

| | |
|------------------|---|
| Catalog Number | HSTT1248Q2 |
| Manufacturer | Panduit Corporation |
| Description | Thin Wall Heat Shrink, .12" (3.2MM) Diameter, Red Cross-Linked Polyolefin, 25 PC. Package Quantity. |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | Insulating Materials |

Features

| | |
|---------------------------------|-----------------|
| continuous operating temperatur | 257 |
| flammability | Flame Retardant |
| Inside Diameter | 0.062 |
| media | Yes |
| outside diameter | 0.125 |
| Shrink Ratio | 2:1 |

Material, Color, and Finish

| | |
|-------|-----|
| Color | Red |
|-------|-----|

Dimensions and Weight

| | |
|-----------|------|
| Thickness | 0.02 |
|-----------|------|

Descriptions

| | |
|------------------------|---|
| Description | HT SHRINK TUBING |
| extra long description | PAN HSTT12-48-Q2 Dry-Shrink™ HSTT12 |
| Long Description | Thin wall heat shrink, .12" (3.2mm) diameter, red cross-linked polyolefin, 25 pc. package quantity. |
| Product Type | Dry-Shrink™ HSTT12-48-Q2 Heat Shrink |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983906031 |
| Manufacturers Part Number | HSTT12-48-Q2 |
| UPC | 074983906031 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | HEAT/COLD SHRINK |
| Type | Heat Shrink Tubing |

Packaging

| | |
|-----------------|----|
| Carton | 25 |
| Weight Per each | 1 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|---|
| Application | For Dry Locations |
| standard | UL Recognized, CSA Approved, MIL SPEC |