



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IC21 6" Shallow Ic Rated Reces

Lithonia Lighting - Acuity

Catalog Number	IC21
Manufacturer	Lithonia Lighting - Acuity
Description	Incandescent Airtight Housing, Round, 75 W, 120 V, Galvanized, Steel Fixture Material, Aluminum Housing Material, Non Dimmable, 6 In Aperture Size, 16.67 LB
Weight per unit	16.7 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	Round
Warranty	1

Dimensions and Weight

Height	5.75
Length	13.125
Width	13.5

Descriptions

Construction	New Construction
Description	6" SHALLOW IC RATED RECES
extra long description	LITH IC21 6IN Incandescent Shallow

Manufacturer Information

Brand	JUNO
GTIN	00661209700230
UPC	661209700230

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
----------------------	---------------------------

Packaging

Carton	1
Package	12
Weight Per each	16.67

Uses, Certifications, and Standards

environmental conditions	Indoor
Mounting	Recessed
standard	CSA,UL