



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IC22R 6" Ic Rated Remodel Reces *Lithonia Lighting - Acuity*

Catalog Number	IC22R
Manufacturer	Lithonia Lighting - Acuity
Description	Incandescent Airtight Housing, Round, 90 W, 120 V, Galvanized, Steel Fixture Material, Aluminum Housing Material, Non Dimmable, 6 In Aperture Size, 1.96 LB
Weight per unit	2.0 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
Shape	Round

Dimensions and Weight

Height	7.125
Length	13.75
Width	7.125

Descriptions

Construction	Remodel
Description	6" IC RATED REMODEL RECES
extra long description	LITH IC22R 6IN Incandescent Remodel

Manufacturer Information

Brand	JUNO
GTIN	00661209017673
UPC	661209017673

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	Housing

Packaging

Carton	1
Package	6
Weight Per each	1.96

Uses, Certifications, and Standards

environmental conditions	Indoor
Mounting	Recessed
standard	cUL,UL