



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IC23W 6" RCS DBL Wall Housing, No Bracket

Lithonia Lighting - Acuity

| | |
|------------------|---|
| Catalog Number | IC23W |
| Manufacturer | Lithonia Lighting - Acuity |
| Description | Incandescent Airtight Housing, Round, 90 W, 120 V, Galvanized, Steel Fixture Material, Aluminum Housing Material, Non Dimmable, 6 In Aperture Size, 19 LB |
| Weight per unit | 19.0 (lbs/each) |
| Product Category | Incandescent Recessed Architec |

Features

| | |
|-------------------------------|--------------|
| Lamp Type | Incandescent |
| Maximum Operating Temperature | 25 |
| Shape | Round |

Dimensions and Weight

| | |
|--------|------|
| Height | 7.75 |
| Length | 13.5 |
| Width | 17.5 |

Descriptions

| | |
|------------------------|-------------------------------------|
| Construction | New Construction |
| Description | 6" RCS DBL WALL HOUSING, NO BRACKET |
| extra long description | LITH IC23 W 6IN Incandescent No Pla |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | JUNO |
| GTIN | 00661209068613 |
| Manufacturers Part Number | IC23 W |
| UPC | 661209068613 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | All Recessed Cans & Trims |
| Type | Housing |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 19 |

Uses, Certifications, and Standards

| | |
|--------------------------|----------|
| environmental conditions | Indoor |
| Mounting | Recessed |
| standard | CSA,UL |