



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ICN2P32N35M 2-F32T8 120/277V Elec Bal

*Advance By Signify*

Catalog Number	ICN2P32N35M
Manufacturer	Advance By Signify
Description	Reliable and Energy Efficient Philips Advance'S Centium Commercial Grade Specifications, Plus Added Benefits Of Lamp Striation Reduction Technology.
Weight per unit	0.7000 (lbs/each)
Product Category	Electronic Linear Fluorescent

### Features

amperage rating	0.49-0.22
ANSI Code	N/A
Ballast Factor	0.88
dimmable	Non Dimmable
Lamp Type	Fluorescent
Number of Lamps	2
Power Factor	0.98
start type	Instant
total harmonic distortion	<=10
Voltage Rating	120-277
Wattage	59

### Material, Color, and Finish

Color	Black
-------	-------

### Dimensions and Weight

Height	3.94
Length	3.74
Width	5.12

### Descriptions

Description	2-F32T8 120/277V ELEC BAL
extra long description	ADV 196873 ELE BALLAST (2) F32T8 12
Long Description	Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology.
Product Type	Ele Ballast (2) F32T8 120-277V
Special Features	IntelliVolt 120-277V, Parallel Lamp Operation

### Manufacturer Information

Brand	Signify Electronics
GTIN	00781087069134
Manufacturers Part Number	ICN2P32N35M
UPC	781087069134



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	ELECTRONIC

## Packaging

Carton	1
Package	30
Weight Per each	0.7

## Uses, Certifications, and Standards

Application	Commercial
Frequency Rating	50to60
Mounting	8.9
standard	CSA certificate;UL certificate;CEC Listing;CEE Rated;CSA E;NEMA Premium;NOM certificate;RoHS Compliant