



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IG5261 Recp SGL 15A 125V S+B Wire Ig

*Pass & Seymour/Legrand*

Catalog Number	IG5261
Manufacturer	Pass & Seymour/Legrand
Description	Isolated Ground Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 15A 125V
Weight per unit	0.1704 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	15
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
Material	Nylon
media	Yes
Number of Wires	3
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

### Material, Color, and Finish

Color	Orange
-------	--------

### Dimensions and Weight

Height	3.68
Width	1.093

### Descriptions

Description	RECP SGL 15A 125V S+B WIRE IG
extra long description	P&S IG5261 RECEPT SINGLE 15A 125V S
Long Description	Isolated Ground Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 15A 125V
Product Type	Recept Single 15A 125V S+B Wire Ig
Special Features	IG symbol and Isolated Ground markings for easy identification and circuit delineation. Triple-wipe brass contacts ensure lasting, positive contact with plug blades. High-impact resistant nylon face resists impacts and scrapes. Corrosion-resistant plated steel strap. Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation. Plastic barrier isolates grounding terminal from mounting strap and metal boxes. Side and internal screw-pressure-plate back wi



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007652611
Manufacturers Part Number	IG5261
UPC	785007652611

## Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Isolated Ground Spec Grade Single Receptacle, Heavy-Duty

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	100
Weight Per each	0.1704

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-15R
standard	CUL, FEDSPEC, UL498, CSA C22.2 No. 42
Temperature Rating	-40° - 60° C