



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IG8300BLSP Ig TVSS HG Recp 20A 125V Alarm BL

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | IG8300BLSP |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Hospital Grade Isolated Ground Surge Protective Duplex Receptacle Offers Increased Transient Protection, Reliability and Protection Notification (Audible Alarm With Led Indicator). Back and Side Wire, 20AMP 125VOLT, Ivory. |
| Weight per unit | 0.3766 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|--|
| amperage rating | 20 |
| class | IG |
| connection | Back and side wire |
| Material | Nylon |
| media | Yes |
| Number of Wires | 3 |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | #14 - #10 |

Material, Color, and Finish

| | |
|-------|------|
| Color | Blue |
|-------|------|

Dimensions and Weight

| | |
|--------|------|
| Height | 3.75 |
| Width | 1.25 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | IG TVSS HG RECP 20A 125V ALARM BL |
| extra long description | P&S IG8300BLSP IG TVSS HG RECP 20A |
| Long Description | Hospital Grade Isolated Ground Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 20amp 125volt, Ivory. |
| Product Type | Ig TVSS HG Recp 20A 125V Alarm BL |
| Special Features | IG symbol and Isolated Ground markings for easy identification and circuit delineation. Plastic barrier isolates grounding terminal from mounting strap and metal boxes. Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place. LED Indication: steady green = protected, flashing red = not protected, OFF = no power to unit. Audible alarm alert of MOV damage. Alarm able to be turned On/Off. Wrap-around steel strap for structural integrity. |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007194623 |
| Manufacturers Part Number | IG8300-BLSP |
| UPC | 785007194623 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Commercial receptacles |
| Type | Isolated Ground Hospital Grade Surge Protective Receptacle, Audible Alarm with LED Indicator |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.3766 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| nema rating | 5-20R |
| standard | CULUS, cUL UL1449, UL498: CSA C22.2 No. 42: ANSI/EEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse). |
| Temperature Rating | Operating Temperature: -20°C to +55°C (-4°F to 131°F), Storage Temperature: -40°C to +85°C (-40°F to 185°F) |