



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IPLD7504 750-250 2S 4 Multi Cable Insul Tap

*Nsi Industries*

Catalog Number	IPLD7504
Manufacturer	Nsi Industries
Description	Double Sided Entry Insulated Multi-Tap Connector, 250 MCM Conductor Size, 750 MCM Conductor Size, Insulated, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, 4 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 6.38 In Overall Length, 600 V, 1.87 LB/Ea
Weight per unit	1.9 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	750-250 MCM
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

### Dimensions and Weight

Size	L=6.380 - W=3.410 - H=3.420
------	-----------------------------

### Descriptions

Description	750-250 2S 4 MULTI CABLE INSUL TAP
extra long description	NSI IPLD750-4 POLARIS Ins Multi-Tap
Features	The Polaris IPLD750-4 4-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to four conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 750 - 250 MCM wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric streng

### Manufacturer Information

GTIN	00662381926029
UPC	662381926029



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Double Sided Entry

## Packaging

Carton	2
Weight Per each	1.87

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C