



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IPLG64 6-14AWG 4PORT MT6 Conn

Nsi Industries

| | |
|------------------|---|
| Catalog Number | IPLG64 |
| Manufacturer | Nsi Industries |
| Description | The Polaris IPLG6-4 Grey Multi-Tap Single Side Entry Connector Features 4 Ports Sized For 6 - 14 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Port Is Specially Designed For Fine-Stranded Copper Wires With A Pre-Installed Tin Plated Copper Ferule That Collapses As The Screw Is Tightened to Form A Strong Connection With Fine-Stranded Wires. Removable Access Plugs Cover The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench |
| Weight per unit | 0.1100 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------------|---|
| Material | Aluminum |
| Number of Conductors | 4 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Size | (Class B,C,D) 6-14 AWG - (Class K,M,I) 6-14 AWG |
| Wire Type | B,C,D,K,M,I |

Material, Color, and Finish

| | |
|--------|---------------------|
| Color | Grey |
| Finish | Plastisol Insulated |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | L=1.980 - W=1.240 - H=1.370 |
|------|-----------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 6-14AWG 4PORT MT6 CONN |
| extra long description | NSI IPLG6-4 POLARIS Grey Multi-Tap |
| Features | The Polaris IPLG6-4 4-Port Single-Side Connector provides the simplest solution for forming a secure connection between up to four fine-stranded wire conductors in applications including cable trays, troughs, wire-ways, raceways, ducts and motor junction boxes. Sized for 6 - 14 AWG wires and rated for 600V, this connector installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric strength plastisol insulation, |
| Long Description | The Polaris IPLG6-4 Grey Multi-Tap Single Side Entry Connector features 4 ports sized for 6 - 14 AWG wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each port is specially designed for fine-stranded copper wires with a pre-installed tin plated copper ferule that collapses as the screw is tightened to form a strong connection with fine-stranded wires. Removable access plugs cover the hex screws used to tighten the connections. Installs with a hex key and torque wrench |
| Product Type | Polaris Grey Multi-Tap 6 4 Port |
| Special Features | (4) 6-14 AWG Class B,C,D - (4) 6-14 AWG Class K,M,I |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Polaris |
| GTIN | 00662381951434 |
| Manufacturers Part Number | IPLG6-4 |
| UPC | 662381951434 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | TERMINALS |
| Type | Single Sided Entry |

Packaging

| | |
|-----------------|------|
| Carton | 6 |
| Weight Per each | 0.11 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Wire Termination |
| environmental conditions | 90 C |
| standard | UL 486A/B |
| Temperature Rating | 90 C |