





REMOVAL BE CAPS FOR  
ACCESS TO 3/16 INTERNAL HEX  
PRESSURE SCREWS



2/0 - #14 AWG  
CONDUCTOR PORTS  
ROCKET USED FOR #1-#14  
DISCARD ROCKET FOR 1/0-2/0



CUT ROCKET AT  
APPROPRIATE STEP  
FOR WIRE SIZE  
USED



PART NO.	NO. OF COND. HOLES	LENGTH
ISPB2/0-2	2	1.93
ISPB2/0-3	3	2.79
ISPB2/0-4	4	3.65
ISPB2/0-6	6	5.37

NOTES:

- DI-ELECTRIC SILICONE FILM ON ROCKET AND CAP FOR EASY ASSY/DISSY.
- PRE-FILLED W/ OXIDE INHIBITOR.
- SHIPPED IN SEALED BAG W/ INSTALL INSTRUCTIONS.

		<b>POLARIS</b> SALES . CO . INC	
PROPRIETARY AND CONFIDENTIAL		11625 PROSPEROUS DRIVE ODESSA, FL 33556	
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POLARIS SALES CO. INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POLARIS SALES CO. INC. IS PROHIBITED.		TITLE: 2/0-#14 STREET LIGHT CONN.	
NAME		DATE	
DRAWN BY L. HILL		4/3/2014	
MATERIAL: N/A		DWG. NO. ISPB 2/0 Series	
SCALE: 1:1		SHEET: 1 OF 1	