



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

760 Ford St.  
80915-0000, CO Colorado Springs  
Phone: 719-559-2456  
Fax: 719-867-4287



## ISR10 1/0 Polaris Insulated Butt SPLC

*Nsi Industries*

Catalog Number	ISR10
Manufacturer	Nsi Industries
Description	Insulated Butt Splice, #14 Awg Conductor Size, #1/0 Awg Conductor Size, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, -45 °C (Cold) Operating Temperature, +90 °C Operating Temperature, 3.25 In Overall Length, 600 V, 0.15 LB
Weight per unit	0.1500 (lbs/each)
Product Category	Splicing & Terminating Kits

### Features

Material	Aluminum
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	1/0-14 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

### Dimensions and Weight

Size	L=3.250 - W=.900 - H=1.480
------	----------------------------

### Descriptions

Description	1/0 POLARIS INSULATED BUTT SPLC
extra long description	NSI ISR-1/0 1/0-14 Awg Polaris Insu

### Manufacturer Information

GTIN	00662381951014
UPC	662381951014

### Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	IN-Line Splicer/Reducer

### Packaging

Carton	4
Weight Per each	0.15



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

760 Ford St.  
80915-0000, CO Colorado Springs  
Phone: 719-559-2456  
Fax: 719-867-4287

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C