Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

10650 West Airport Suite 100
77477-0000, TX Stafford
Phone: 281-879-4911
Fax: 281-879-8596



ISR250 250MCM Polaris Insulated Butt SPLC

Nsi Industries

Catalog Number	ISR250
Manufacturer	Nsi Industries
Description	Insulated Butt Splice, #6 Awg Conductor Size, 250 MCM Conductor Size, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, -45 °C (Cold) Operating Temperature, +90 °C Operating Temperature, 4 In Overall Length, 600 V, 0.34 LB
Weight per unit	0.3400 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Material	Aluminum
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	250 MCM-6 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

Dimensions and Weight

Size	L=4.000 - W=1.190 - H=1.900

Descriptions

Description	250MCM POLARIS INSULATED BUTT SPLC
extra long description	NSI ISR-250 250 Mcm-6 Awg Polaris

Manufacturer Information

GTIN	00662381951021
UPC	662381951021

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	IN-Line Splicer/Reducer

Packaging

Carton	4
Weight Per each	0.34

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
10650 West Airport Suite 100
77477-0000, TX Stafford
Phone: 281-879-4911
Fax: 281-879-8596

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C