



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ISRH750 750 MCM Splice

*Nsi Industries*

Catalog Number	ISRH750
Manufacturer	Nsi Industries
Description	The Polaris Isrh-750 Heavy-Duty Multi-Tap In-Line Entry Connector Features 2 Ports Sized For 750 MCM 1/0 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Double Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies, and Comes Packaged In A Clear Plastic Bag With A Mounting Hole For Hanging In Retail Disp
Weight per unit	1.9 (lbs/each)
Product Category	Splicing & Terminating Kits

### Features

Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	750-250 MCM
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated
Housing Material	Aluminum

### Dimensions and Weight

Size	L=7.250 - W=1.750 - H=3.250
------	-----------------------------



## Descriptions

Description	750 MCM SPLICE
extra long description	NSI ISRH-750 POLARIS Ins Splice HD
Features	The Polaris ISRH-750 2-Port In-Line Connector provides the simplest solution for forming a secure, heavy-duty connection between two conductors in splicing and reducing applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 750 MCM â€" 1/0 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrap
Long Description	The Polaris ISRH-750 Heavy-Duty Multi-Tap In-Line Entry Connector features 2 ports sized for 750 MCM â€" 1/0 AWG wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each port is pre-loaded with an oxide inhibitor, with removable access plugs over the double hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies, and comes packaged in a clear plastic bag with a mounting hole for hanging in retail disp
Product Type	Polaris Ins Splice HD 750
Special Features	750-250 MCM - Dual Rated

## Manufacturer Information

Brand	Polaris
GTIN	00662381926456
Manufacturers Part Number	ISRH-750
UPC	662381926456

## Taxonomies, Classifications, and Categories

Type	IN-Line Splicer/Reducer
------	-------------------------

## Packaging

Carton	2
Weight Per each	1.85

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B