



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IT10C 1/0-14AWG 2PRT Insld Tap Conn

Nsi Industries

| | |
|------------------|--|
| Catalog Number | IT10C |
| Manufacturer | Nsi Industries |
| Description | The Polaris It-1/0C Multi-Tap Single-Side Entry Vision Tap Connector Features 2 Ports Sized For 1/0 - 14 Awg Wires. The Clear Body Allows Users to See Their Conductor Placement and Is Wrapped In A Layer Of Plastisol Insulation. Each Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including |
| Weight per unit | 0.1300 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------------|-------------|
| Material | Aluminum |
| Number of Conductors | 2 |
| Poles | 1 |
| Voltage Rating | 600 |
| Warranty | 1 YEAR |
| Wire Size | 1/0-14 AWG |
| Wire Type | Class B & C |

Material, Color, and Finish

| | |
|--------|---------------------|
| Color | Clear |
| Finish | Plastisol Insulated |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | L=1.620 - W=1.620 - H=1.750 |
|------|-----------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 1/0-14AWG 2PRT INSLTD TAP CONN |
| extra long description | NSI IT-1/0C POLARIS Vision Tap 2 Po |
| Features | The Polaris IT-1/0C 2-Port Single-Side Connector provides the simplest solution for forming a secure connection between two conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 1/0 - 14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The clear body lets installers see their work for optimal conductor p |
| Long Description | The Polaris IT-1/0C Multi-Tap Single-Side Entry Vision Tap Connector features 2 ports sized for 1/0 - 14 AWG wires. The clear body allows users to see their conductor placement and is wrapped in a layer of plastisol insulation. Each port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including |
| Product Type | Polaris Vision Tap 2 Port 1/0 |
| Special Features | (2) 1/0-14 AWG - Dual Rated |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Polaris |
| GTIN | 00662381996411 |
| Manufacturers Part Number | IT-1/0C |
| UPC | 662381996411 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | TERMINALS |
| Type | Single Sided Entry |

Packaging

| | |
|-----------------|------|
| Carton | 6 |
| Weight Per each | 0.13 |

Uses, Certifications, and Standards

| | |
|--------------------------|-------------------|
| Application | Wire Termination |
| Enclosure | Clear Plastisol |
| environmental conditions | Dry Location Only |
| standard | UL 486A/B |
| Temperature Rating | 90 |