

## "J" Series Configurations

**FHPL** Fiberglass hinged, flush bonded window, padlock latch

### Design Features

- Fiberglass hinge for maximum corrosion resistance
- Removable lift off cover capability
- Padlock latch for quick entry and added security
- Full 180°+ door opening



J SERIES

### "STAHLIN INFORMATION CENTER"


Stahlin's "J" Series includes a hybrid design using a slightly elevated cover called a "crown cover". It's purpose is to create a slightly greater overall depth dimension by increasing the depth of the cover. This design is available in a 10x8 size only and complements all the standard configurations including: screw down, padlock or twist lock latched, non metallic hinged and windowed versions.

The crown cover is a designer favorite for its unique shape as well as the utility of its extra depth.

#### Crowned Cover Catalog Numbers

Catalog #	Description	Page
<a href="#">J1008WA</a>	Crowned Cover, 4 cover screws, lift off cover	114
<a href="#">J1008HWA</a>	Crowned Cover, Hinged, 2 cover screws	116
<a href="#">J1008HALL</a>	Crowned Cover, Hinged, link lock latch	118
<a href="#">J1008HAPL</a>	Crowned Cover, Hinged, padlock latch	120
<a href="#">J1008FHWA</a>	Crowned Cover, Fiberglass hinged, 4 cover screws	122
<a href="#">J1008FHALL</a>	Crowned Cover, Fiberglass hinged, link lock latch	124
<a href="#">J1008FHAPL</a>	Crowned Cover, Fiberglass hinged, padlock latch	126

J Series Crowned Covered technical data is covered in greater detail on the appropriate configuration page.



Crowned cover offers 3/4" more in depth than the standard Flat cover.