

Eaton JGE3250NN

Catalog Number: JGE3250NN

Eaton molded case circuit breaker accessory frame, Frame only, 250 A, 65 kAIC at 240 V, 25 kAIC at 480 V, 18 kAIC at 600 V, Three-pole, 600 V, Frame only (no trip), Frame J-K, Series G

General specifications



Photo is representative

Product Name	Catalog Number
Eaton molded case circuit breaker accessory frame	JGE3250NN
	UPC
	782116008612
Product Length/Depth	Product Height
3.57 in	7 in
Product Width	Product Weight
4.13 in	6 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year CE Marked from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	CSA Certified
	IEC Rated
	UL Listed

defaultTaxonomyAttributeLabel

Type

Frame only

Amperage Rating

250 A

Voltage rating

600 V

Trip Type

Frame only (no trip)

Frame size

Frame J-K

Series

Series G

Interrupt rating

25 kAIC at 480 V

18 kAIC at 600 V

65 kAIC at 240 V

Number of poles

Three-pole

Resources

Application notes

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

Brochures

[Multi-wire lugs product aid](#)

[Current limiting molded case circuit breaker module product aid](#)

[StrandAble terminals product aid](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Motor protection circuit breakers product aid](#)

[Comprehensive circuit protection for control panel applications](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Series G MCCB quick selector](#)

[Circuit breaker motor operators product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Breaker service centers](#)

[J-Frame 310+ and L-Frame 310+ Molded-case circuit breakers](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Drawings

[JG-frame Molded Case Circuit Breaker Drawing](#)

[AB DE-ION CIRCUIT BREAKER TYPE JG BRKR JG CURR LIMITER 3 POLE OUTLINE](#)

Installation instructions

[Installation Instructions for Series G J-Frame Circuit Breakers](#)

Multimedia

[Flex shaft handle installation tutorial](#)

Specifications and datasheets

[Series G, J-frame Time Current Curve](#)

[Eaton Specification Sheet - JGE3250NN](#)

[NG and ND-Frame molded case circuit breakers](#)

[MOEM MCCB product selection guide](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)