

Eaton JJS-30

Catalog Number: JJS-30

Eaton Bussmann series JJS fuse, Current-limiting, Small footprint, VFD line protection, 30 A, Class T, Non-indicating, Ferrule end x ferrule end, 200 kAIC at 600 V, Standard, 10, 600 V



General specifications

| | |
|--------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton Bussmann series JJS fuse | JJS-30 |
| UPC | Product Length/Depth |
| 051712628006 | 1.5 in |
| Product Height | Product Width |
| 0.56 in | 0.56 in |
| Product Weight | Warranty |
| 0.15 lb | Not Applicable |
| Compliances | |
| CE Marked | |
| RoHS Compliant | |

Electrical rating

Amperage Rating

30 A

Interrupt rating

200 kAIC at 600 Vac

Voltage rating

600 V

Physical details

Packaging type

Standard

General information

Class

Class T

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Non-indicating

Resources

Catalogs

Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - JJS-30

Technical data sheets

JJS-30~TRON FAST ACTING FUSE CLASS T

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)