



BURNDY Catalog Number
UPC Number

K2A36U
7818106002077
TWO:2 STR-600 DUAL RTD,1/2 IN
Bolt Hole
Active

Description
Status

Web Use
BURNDY Product Line

Dimensional

Width (in)	2.41
Length (in)	3.20
Bolt Hole Size (in)	0.50
Thickness	0.44
D - in	1.75
Pad Width (in)	2.42
N (in)	0.63

General

Number of Conductors	2
Number of Holes	1
Product Description	Aluminum Universal Terminal, 2 Conductor, 1 Hole, 2 AWG (Str)-600 kcmil, 1/2" Stud, 2 Screws, Al/Cu Rated, Tin Plated

Conductor(s)

Aluminum Size (Range)	2 STR- 600 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	2 AWG-600 kcmil

Physical

Installation Torque	375
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	1/2
Plated (Yes or No)	N
Product Material	Aluminum

Approvals / Certifications

Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175



BURNDY Catalog Number
UPC Number

K2A36U
 7818106002077
 TWO:2 STR-600 DUAL RTD,1/2 IN
 Bolt Hole
 Active

Description
Status

Web Use
 BURNDY Product Line

Dimensional

Width (in)	2.41
Length (in)	3.20
Bolt Hole Size (in)	0.50
Thickness	0.44
D - in	1.75
Pad Width (in)	2.42
N (in)	0.63

General

Number of Conductors	2
Number of Holes	1
Product Description	Aluminum Universal Terminal, 2 Conductor, 1 Hole, 2 AWG (Str)-600 kcmil, 1/2" Stud, 2 Screws, Al/Cu Rated, Tin Plated

Conductor(s)

Aluminum Size (Range)	2 STR- 600 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	2 AWG-600 kcmil

Physical

Installation Torque	375
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	1/2
Plated (Yes or No)	N
Product Material	Aluminum

Approvals / Certifications

Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175