



BURNDY Catalog Number
UPC Number
Description
Status

K2C17
 7818102569099
 10-7 STR 3/8 POST 2 COND
 Active

Web Use
 BURNDY Product Line

Dimensional

Stud Length (in)	3/8,0.37
Thread Size	1/4-20
Height (in)	0.84
D or Diameter (Fraction) (in)	1/2
Nut Width (Fraction)	5/8
Nut Width (in)	0.62
D - in	0.50
Body Width (Fraction)	7/16
Body Width (in)	0.44
Height (Fraction) (in)	7/8

General

Product Description
 Mechanical Grounding Connector,
 2 Cables to Flat, 10 - 7 AWG (Str)
 / 10 - 6 AWG (Sol)

Conductor(s)

Copper Solid Size (Range)	10 AWG-6 AWG
Copper Stranded (Range)	10 AWG-7 AWG

Physical

Type of Plating	Unplated
Plated (Yes or No)	N
Product Material	Leaded Bronze Alloy

Approvals / Certifications

Rated for Direct Burial	Y
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N
Industry Standards	UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175