



Stem Mounting, Thermal Type — K4100 Series

This series features single and multivolt models in both stem mount and stem mount with a swivel. All models are equipped with a light level slide adjustment and provide a 1/2"-14 threaded stem. A washer gasket and locking nut are packaged with each photo control. Models with "M" suffix have heavy duty die cast housings. Model K4251 and K4253 have photo eye located on top and are designed for spot/flood type fixtures.

Size – K4100 Series - 1-9/16" (4.0 cm) Square, 3" (7.6 cm) Long;

K4200 Series - 1/2"-14 threaded swivel, 1-9/16" (4.0 cm) Square, 5-1/2" (14.0 cm) Long;

Model K4236 - 5-3/4" (14.6 cm) High, 3" (7.6 cm) Diameter.

Model #	Watts Tungsten	VA Ballast	Amps Tungsten	Amps Ballast	Volts
K4121C	1800	1000	15	8.3	120
K4121M	2000	1800	16.7	15	120
K4421M	1800	1000	15	8.3	120
K4124	3100	1700	15	8.3	208
K4122	3600	2000	15	8.3	240
K4123C	3100-4150	1700-2300	15	8.3	208-277
K4423M***	3100-4150	1700-2300	15	8.3	208-277
K4133	4150	2300	15	8.3	277
K4127****	5205	2880	15	8.3	347
K4135*	7200	4000	15	8.3	480
K4136M	2000-4625	1800	16.7	8.6	120 or 277
**K4141C*	3000	3000	25	25	120

* Not UL listed or CSA certified.

** 1 year warranty.

*** Model K4423M replaces K4123M

**** Certified by CSA to US and Canadian Standards.



UL773A
E42722



C22.2-55
LR38068



5 Year
Warranty

Stem & Swivel Mounting, Thermal Type — K4200 Series

Model #	Watts Tungsten	VA Ballast	Amps Tungsten	Amps Ballast	Volts
K4221C	1800	1000	15	8.3	120
K4224	3100	1700	15	8.3	208
K4222	3600	2000	15	8.3	240
K4223C	3100-4150	1700-2300	15	8.3	208-277
K4233	4100	2300	15	8.3	277
K4227****	5205	2880	15	8.3	347
K4235*	7200	4000	15	8.3	480
K4236C	1800-4150	1000-2300	15	8.3	120 or 208-277
K4251***	1800	1000	15	8.3	120
K4253***	3100-4150	1700-2300	15	8.3	208-277

* Not UL listed or CSA certified.

*** Certified by CSA to US and Canadian Standards.



UL773A
E42722



C22.2-55
LR38068



5 Year
Warranty



C22.2-177
LR3730