









U5000 STANDARD MODELS






CATALOG #	RECEPTACLES		CIRCUIT BREAKERS	
◆ U5000-XL-41	(1) TT30R (1) 5-20R GFI		(1) 30A, 1P, 120V (1) 20A, 1P, 120V	
◆ U5000-XL-332	(2) TT30R (1) 5-20R GFI		(2) 30A, 1P, 120V (1) 20A, 1P, 120V	
◆ U5000-XL-55	(1) 14-50R (1) 5-20R GFI		(1) 50A, 2P, 120/240V (1) 20A, 1P, 120V	
◆ U5000-XL-75	(1) 14-50R (1) TT30R (1) 5-20R GFI		(1) 50A, 2P, 120/240V (1) 30A, 1P, 120V (1) 20A, 1P, 120V	
U5000-XL-75GB	(1) 14-50R (1) TT30R (1) 5-20R		(1) 50A, 2P, 120/240V (1) 30A, 1P, 120V (1) 20A, 1P, 120V, GFI	

U5000 STANDARD BASE MODEL

Order up to (3) receptacle / breaker kits. Sold separately for field installation.

CATALOG #	DESCRIPTION
◆ U5000-XL	Base model without receptacles or circuit breakers.

RECEPTACLE & CIRCUIT BREAKER KITS

CATALOG #	RECEPTACLES	CIRCUIT BREAKERS	CONDUCTORS	CONFIGURATION
◆ K5400-520GR	5-20R Duplex GFI	20 Amp, 1 Pole	12 Awg	 GFI Rec.
◆ K5400-520GB	5-20R Duplex	20 Amp, 1 Pole GFI	12 Awg	 GFI CB
◆ K5400-TT30	TT30R	30 Amp, 1 Pole	10 Awg	
K5400-TT30GB	TT30R	30 Amp, 1 Pole GFI	10 Awg	 GFI CB
◆ K5400-1450	14-50R	50 Amp, 2 Pole	8 Awg	

◆ Stock model. Availability subject to prior sale.

Note: 20 Amp GFI required at each RV site by UL and NEC 551-71

INTERNAL LIGHT KITS Factory or field installed. See accessory page.

Utility requirements for this equipment may vary. Always consult the serving utility for their requirements before ordering or installing equipment in this catalog.