

# Eaton KRP-C-800SP

Catalog Number: KRP-C-800SP

Eaton Bussmann series KRP-C fuse, Current-limiting time-delay fuse, 800 A, L, Non-indicating, Bolted blade end x bolted blade end, 4 sec at 500%, 300 kAIC at 600 V, 100 kA at 300 kAIC Vdc, 600 V, 300 Vdc



## General specifications

Product Name	Catalog Number
Eaton Bussmann series KRP-C fuse	KRP-C-800SP
UPC	Product Length/Depth
051712605083	8.63 in
Product Height	Product Width
2.53 in	2.53 in
Product Weight	Warranty
3.8 lb	Not Applicable

## Compliances

CE Marked  
RoHS Compliant

## Electrical rating

### Amperage Rating

800 A

### Interrupt rating

300 kAIC at 600 Vac

100 kA at 300 kAIC Vdc

### Response time

4 sec at 500%

### Voltage rating

600 Vac, 300 Vdc

## Physical details

### Packaging type

Standard

## General information

### Class

Class L

### Connection

Bolted blade end x bolted blade end

### Fuse indicator

Non-indicating

### Special features

Small footprint

## Resources

### Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - KRP-C-800SP](#)

### Technical data sheets

[KRP-C-800SP~LOW-PEAK TIME-DELAY 300K](#)

### Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton KRP-C-800SP

Catalog Number: KRP-C-800SP

Eaton Bussmann series KRP-C fuse, Current-limiting time-delay fuse, 800 A, L, Non-indicating, Bolted blade end x bolted blade end, 4 sec at 500%, 300 kAIC at 600 V, 100 kA at 300 kAIC Vdc, 600 V, 300 Vdc



## General specifications

Product Name	Catalog Number
Eaton Bussmann series KRP-C fuse	KRP-C-800SP
UPC	Product Length/Depth
051712605083	8.63 in
Product Height	Product Width
2.53 in	2.53 in
Product Weight	Warranty
3.8 lb	Not Applicable

## Compliances

CE Marked  
RoHS Compliant

## Electrical rating

### Amperage Rating

800 A

### Interrupt rating

300 kAIC at 600 Vac

100 kA at 300 kAIC Vdc

### Response time

4 sec at 500%

### Voltage rating

600 Vac, 300 Vdc

## Physical details

### Packaging type

Standard

## General information

### Class

Class L

### Connection

Bolted blade end x bolted blade end

### Fuse indicator

Non-indicating

### Special features

Small footprint

## Resources

### Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - KRP-C-800SP](#)

### Technical data sheets

[KRP-C-800SP~LOW-PEAK TIME-DELAY 300K](#)

### Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)