



KS20, Split Bolt Connector, Run/Tap: #8 AWG Str-#4 AWG Sol

By Burndy
Catalog # [KS20](#)

Copper Split Bolt, Cu: 8 AWG (Str)-4 AWG (Sol) (Run & Tap),Length:1.20.



Application

For Direct Burial Applications In Earth Or Concrete, Copper

General

EU RoHS Indicator	Yes
Sub Brand	SERVIT
Type	KS, Compact
UPC	781810012000

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	99000

Product Assets

[3D Models - KS20_MODEL-IGES](#)
[3D Models - KS20_MODEL-STEP](#)
[3D Models - KS20_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..078561-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-KS20-SPEC-EN | REV 8/2023