

BURNDY Catalog Number
UPC Number
Description
Status

KS22
 7818100125055
 SERVIT 6 STR - 2 SOL
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in) 0.60
 Size (Hex) or Size (Bolt) 19/32
 Cross Flats 0.75
 Size (Hex) or Size (Bolt) - in 0.594
 B Length (in) .69
 B Length (Fraction) 69/100

General

Product Description

Copper Split Bolt, Cu: 6 AWG
 (Str)-2 AWG (Sol) (Run & Tap)

Conductor(s)

Copper Tap Range 14 AWG-2 AWG
 CopperWeld Solid Run Size (Range) #2
 Copper Stranded Run (Range) 6 AWG-2 AWG
 CopperWeld Stranded Tap Size (Range) 6 D AWG-4 A AWG
 Copper Solid Tap (Range) 14 AWG-2 AWG
 CopperWeld Solid Tap Size (Range) #2
 Copper Solid Run Size (Range) 6 AWG-2 AWG
 CopperWeld Stranded Run Size (Range) 3#8-6D

Physical

Installation Torque 275
 Type of Plating Unplated
 Connector Type Split Bolt
 Plated (Yes or No) N
 Product Material Copper

Approvals / Certifications

Rated for Direct Burial Y
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL 486A, UL486B

Documentation

For further technical assistance, please contact us


BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175



BURNDY Catalog Number
UPC Number
Description
Status

KS22
 7818100125055
 SERVIT 6 STR - 2 SOL
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in) 0.60
 Size (Hex) or Size (Bolt) 19/32
 Cross Flats 0.75
 Size (Hex) or Size (Bolt) - in 0.594
 B Length (in) .69
 B Length (Fraction) 69/100

General

Product Description

Copper Split Bolt, Cu: 6 AWG
 (Str)-2 AWG (Sol) (Run & Tap)

Conductor(s)

Copper Tap Range 14 AWG-2 AWG
 CopperWeld Solid Run Size (Range) #2
 Copper Stranded Run (Range) 6 AWG-2 AWG
 CopperWeld Stranded Tap Size (Range) 6 D AWG-4 A AWG
 Copper Solid Tap (Range) 14 AWG-2 AWG
 CopperWeld Solid Tap Size (Range) #2
 Copper Solid Run Size (Range) 6 AWG-2 AWG
 CopperWeld Stranded Run Size (Range) 3#8-6D

Physical

Installation Torque 275
 Type of Plating Unplated
 Connector Type Split Bolt
 Plated (Yes or No) N
 Product Material Copper

Approvals / Certifications

Rated for Direct Burial Y
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL 486A,UL486B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175