



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## KS39 750MCM Split Bolt Conn

Burndy LLC

Catalog Number	KS39
Manufacturer	Burndy LLC
Description	Copper Split Bolt, Cu: 4/0 Awg (STR)-750 Kcmil (Run & Tap).
Weight per unit	1.7 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper
----------	--------

### Descriptions

Description	750MCM SPLIT BOLT CONN
extra long description	BUR KS39 SERVIT 4/0 STR - 750
Long Description	Copper Split Bolt, Cu: 4/0 AWG (Str)-750 kcmil (Run & Tap).
Product Type	Mechanical
Special Features	Features: Compact, High Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Season Cracking And Corrosion, The SERVIT Provides Maximum Pressure And Assures A Secure Connection On All Combinations Of Run And Tap Conductors, Installation Torque: 1000 IN-LB, Conductor Type: Run: Commercial Stranded And Solid Copper, Stranded Copperweld, Tap: Commercial Stranded And Solid Copper, Stranded Copperweld, Length: 3.29 IN, Width: 1.94 IN, Cross FI

### Manufacturer Information

Brand	BURNDY
GTIN	00781810014752
Manufacturers Part Number	KS39
UPC	781810014752

### Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	KS

### Packaging

Carton	1
Weight Per each	1.7383

### Uses, Certifications, and Standards

Application	For Direct Burial Cables
standard	UL 486A;UL486B