



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## KTLED15T848GC850 15W Led T8 48" 50K Line Voltage

*Keystone Technologies*

Catalog Number	KTLED15T848GC850
Manufacturer	Keystone Technologies
Description	15W Led T8 Tube, Shatter-Proof Coated Glass, 120-277V Input, 4, 5000K, Direct Drive
Weight per unit	0.0256 (lbs/each)
Product Category	Shape & Circular Lamps

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	2000
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	15
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

### Descriptions

Construction	Frosted Shatterproof Glass
Description	15W LED T8 48" 50K LINE VOLTAGE
extra long description	Key KT-LED15T8-48GC-850-D /G3-CP 15
Long Description	15W LED T8 TUBE, SHATTER-PROOF COATED GLASS, 120-277V INPUT, 4, 5000K, DIRECT DRIVE
Product Type	15W, 2000 Lumen, 4', 240' Beam Angle, Ballast Bypass, DLC 4.

### Manufacturer Information

Brand	Keystone
GTIN	00890949013335
Manufacturers Part Number	KT-LED15T8-48GC-850-D /G3-CP
UPC	890949013335



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	------------------------------------------------------------------

## Packaging

Carton	1
Weight Per each	0.0256

## Uses, Certifications, and Standards

Energy Star	N
-------------	---