



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KTSP10KV 120-277V 10KV Surge

Keystone Technologies

| | |
|------------------|--|
| Catalog Number | KTSP10KV |
| Manufacturer | Keystone Technologies |
| Description | External Surge Protector, Parallel Wiring; Input Voltage 120-277V, Max Peak Protection Rating (10KV, 10KA), IP67 Rated |
| Weight per unit | 0.3100 (lbs/each) |
| Product Category | Surge Suprsr-Prot Dev-LN Condi |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | N/A |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | N/A |
| Nominal Length | N/A |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | N/A |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|-----|
| Base Type | N/A |
| color rendering index (cri) | N/A |
| color temperature | N/A |
| housing color | N/A |

Descriptions

| | |
|------------------------|--|
| Construction | N/A |
| Description | 120-277V 10KV SURGE |
| extra long description | Key KTSP-10KV External Surge Protec |
| Long Description | EXTERNAL SURGE PROTECTOR, PARALLEL WIRING; INPUT VOLTAGE 120-277V, MAX PEAK PROTECTION RATING (10KV, 10KA), IP67 RATED |
| Product Type | External Surge Protector, 10KV, Parallel Wiring |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Keystone |
| GTIN | 00890949012208 |
| Manufacturers Part Number | KTSP-10KV |
| UPC | 890949012208 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 40 |
| Weight Per each | 0.31 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | N |
|-------------|---|