

# Eaton KTS-R-10

Catalog Number: KTS-R-10

Eaton Bussmann series KTS-R fuse, 70/30 brass end cap, Panelboards, 10 A, 1, Class RK1, Non-indicating, Ferrule end x ferrule end, 200 kAIC at 600 Vac, Melamine glass tube, Standard, 600 V



## General specifications

Product Name	Catalog Number
Eaton Bussmann series KTS-R fuse	KTS-R-10
UPC	EAN
051712417037	5027590446303
Product Length/Depth	Product Height
0.8 in	5 in
Product Width	Product Weight
0.8 in	0.13 lb
Warranty	Compliances
Not Applicable	CE Marked

## Electrical rating

### Amperage Rating

10 A

### Interrupt rating

200 kAIC at 600 Vac

### Voltage rating

600 V

## Physical details

### Material

Melamine glass tube

### Number of elements

1

### Packaging type

Standard

## General information

### Class

Class RK1

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Special features

70/30 brass end cap

## Resources

### Catalogs

[Bussmann series complete full line catalog no. 1007](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - KTS-R-10](#)

### Technical data sheets

[KTS-R-10-LIMITRON FAST ACTING FUSE CLASS RK1](#)

[Bussmann series KTS-R 600 V Class RK1 fuse data sheet no. 1044](#)

### Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)