



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KV1410RM 16-14AWG Ins Ring Term

Abb Installation Products, Inc

| | |
|------------------|---|
| Catalog Number | KV1410RM |
| Manufacturer | Abb Installation Products, Inc |
| Description | Vinyl Insulated Ring Terminal, Length .898 Inches, Width .335 Inches, Bolt Hole #10, Wire Range #16-#14 Awg, Color Blue, Copper, Tin Plated |
| Weight per unit | 0.0030 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|-----------|
| Material | Copper |
| Voltage Rating | 600 V |
| Wire Size | 16-14 AWG |

Material, Color, and Finish

| | |
|-------|------|
| Color | Blue |
|-------|------|

Descriptions

| | |
|------------------------|---|
| Description | 16-14AWG INS RING TERM |
| extra long description | ABB KV14-10R-M VINYL RNG TERMINAL, |
| Long Description | Vinyl Insulated Ring Terminal, Length .898 Inches, Width .335 Inches, Bolt Hole #10, Wire Range #16-#14 AWG, Color Blue, Copper, Tin Plated |
| Product Type | Vinyl RNG Terminal, 16-14, NO10 Stu |
| Special Features | Molded Funnel Entry Insulator. Brazed Seam. Internal Barrel Serrations |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Sta-Kon |
| GTIN | 00786210100685 |
| Manufacturers Part Number | KV14-10R-M |
| UPC | 786210100685 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | TERMINALS |
| Type | Vinyl Insulated Ring Terminal |

Availability

| | |
|-------------|------|
| minimum qty | 1000 |
|-------------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 1000 |
| Weight Per each | 0.003 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

UL E9809 / UL E9809
