

# 30 Amp NEMA L1030 Single Receptacle

L1030R



Turnlok Single Receptacle 3wire 30amp  
125/250v



## features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

## specifications

### General Info

Type: Single, Receptacles  
Number Of Wires: 3

### Listing Agencies/Third Party Information

CSA Listing Info: No  
CUL Listing No: No  
cURus: No  
Federal Spec: Yes  
Fed Spec Number: WC596

UL Listing No: 498  
UL Standard: Yes  
UN SPS C: 39121403  
UR: No

**Dimensions**

Depth U S: 1.28"  
Height U S: 3.28"  
Width U S: 1.61"

**Technical Information**

Amps: 30 Amp  
NEMA Configuration Number: L1030  
Volts: 125/250V  
Volts A C: 125/250

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant