



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2450 NE Inner Loop Building 1
78626-0000, TX Georgetown
Phone: 737-444-2615
Fax: 737-444-2617



L11T848GC840SG3 11W Led T8 48" 40K Ballast Compatible - Coated GLS

Keystone Technologies

Catalog Number	L11T848GC840SG3
Manufacturer	Keystone Technologies
Description	11W Led T8 Tube, Shatter-Proof Coated Glass, Ballast Compatible, 4 FT., 4000K, Smartdrive
Weight per unit	0.0263 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	240
Circuit Type	N/A
Input Voltage	Ballast Dependent
ip rating	N/A
Lamp Type	T8
lumens	1800
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	11
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Construction	Frosted Shatterproof Glass
Description	11W LED T8 48" 40K BALLAST COMPATIBLE
extra long description	Key KT-LED11T8-48GC-840-S /G3 11W L
Long Description	11W LED T8 Tube, Shatter-Proof Coated Glass, Ballast Compatible, 4 ft., 4000K, SmartDrive
Product Type	11W Led T8 Tube, Shatter-Proof Coated Glass, Ballast Compati

Manufacturer Information

Brand	Keystone
GTIN	00843654136301
Manufacturers Part Number	KT-LED11T8-48GC-840-S /G3
UPC	843654136301



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2450 NE Inner Loop Building 1
78626-0000, TX Georgetown
Phone: 737-444-2615
Fax: 737-444-2617

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	25
Weight Per each	0.0263

Uses, Certifications, and Standards

Energy Star	N
-------------	---