



# LED Beveled Face Color & Wattage Selectable Downlights

## Product Specifications



For quick, easy, and affordable LED upgrades, switch to TCP's LED Downlights. TCP's Beveled Face Color & Wattage Selectable Downlights have both E26 and direct wire options, PMMA plastic to prevent lens discoloration, and quick-snap holding arms to quickly attach to a recessed can. With a traditional look, these downlights provide smooth, even light in the color temperature you need.

### Reasons to choose the LED Beveled Face Color & Wattage Selectable Downlights from TCP

- Color selectable — choose between 2700K/3000K/3500K or 3000K/4000K/5000K
- Wattage selectable — choose between 8W, 10.5W and 14.5W
- Excellent color consistency and CRI enhances colors of the focal point while maintaining uniformity through-out the lighting installation
- Smooth, uniform dimming 100 - 10%
- Long, 50,000 hour life minimizes replacement and maintenance costs
- Very low heat generation makes the downlight perfect for sensitive display lighting
- Durable PMMA plastic housing resists discoloration
- Easy installation – mounts directly to a 6" recessed can and includes both E26 and direct wire power options
- Energy Star Certified


### Ideal Applications

- Commercial
- Industrial
- Retail
- Residential
- Healthcare

### Specifications

Color Temperatures ..... 2700K/3000K/3500K or 3000K/4000K/5000K  
 Wattage options ..... 8W, 10.5W, 14.5W  
 Input Line Voltage ..... 120 VAC  
 Input Line Frequency..... 50/60HZ  
 Lamp Life (Rated) ..... 50,000 hours

Minimum Starting Temp .....-22°F/-30°C  
 Maximum Operating Temp.....104°F/40°C  
 CRI.....80  
 IC-rated for direct contact with insulation  
 UL approved for damp location (indoor only)—outdoor environment may cause yellowing of the white trim. This is not covered by warranty.



## Specifications



6 inch Dimmable Downlight

ITEM #	DESCRIPTION	VOLTAGE	WATTS	INCANDES. WATTS	LPW	LUMENS	COLOR	MOL CRI	DIA (inches)	BEAM ANGLE	BASE	ENERGY STAR	WARRANTY YEARS	
<b>LED 120W Equivalent Options</b>														
<b>DR56 Downlight • Dimmable • 50,000 Hour</b>														
L120DR56DCCT1	5"/6" LED Beveled Face Color & Wattage Selectable Downlight 2700K/3000K/3500K	120V	8/10.5/14.5	120	8W: 95.6/106.3/106.3 10.5W: 95.2/104.8/104.8 14.5W: 86.9/96.6/96.6	8W: 765/850/850 10.5W: 1000/1100/1100 14.5W: 1260/1400/1400	2700K/3000K/3500K	80	3.0	7.4	120°	E26	★	5
L120DR56DCCT2	5"/6" LED Beveled Face Color & Wattage Selectable Downlight 3000K/4000K/5000K	120V	8/10.5/14.5	120	8W: 113.8/118.1/115 10.5W: 104.8/110.5/106.7 14.5W: 100/95.5/102.3	8W: 910/945/920 10.5W: 1100/1160/1120 14.5W: 1450/1370/1490	3000K/4000K/5000K	80	3.0	7.4	120°	E26	★	5

# TECHNOLOGY CAST IN A BEAUTIFUL LIGHT

For over 20 years, TCP has been designing, developing and delivering energy-efficient lighting into the market. Thanks to our cutting-edge technology and manufacturing expertise, we have shipped billions of high quality lighting products. With TCP, you can count on a lighting product that is designed to meet the needs of the market - that transforms your surroundings and envelopes you in warmth - lighting that generates beauty with every flip of the switch.

Sales:

Date:

Model:

Project:

Rep:

Catalog Number:

Type:

Notes:



For more information on the quality and care TCP can deliver, call us at **800.324.1496** or visit [tcp.com](http://tcp.com)

325 Campus Dr. | Aurora, Ohio 44202 | P: 800.324.1496 | F: 877.487.0516