



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L1430FI Flanged Inlet 4W 30A 125/250V T/L *Pass & Seymour/Legrand*

Catalog Number	L1430FI
Manufacturer	Pass & Seymour/Legrand
Description	Locking Device Turnlock Flanged Inlet, 30 A, 125/250 V Ac, 2 Poles, 3 Wires, Black/White, Nylon Material, -40 °C Operating Temperature, +75 °C Operating Temperature, 3.12 In;0.225 to 1.150 In (Cord) Diameter, Flanged, 1.75 In Length, #18 to #8 Awg Wire Size, Impact and Corrosion Resistant, 0.26 LB
Weight per unit	0.2640 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	30
Poles	2

### Material, Color, and Finish

Color	Black&White
-------	-------------

### Dimensions and Weight

Size	3.1 in
------	--------

### Descriptions

Description	FLANGED INLET 4W 30A 125/250V T/L
extra long description	P&S L1430FI FLANGED INLET 4W 30A 12

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007143027
Manufacturers Part Number	L1430FI
UPC	785007143027

### Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Turnlock Flanged Inlet

### Packaging

Carton	1
Package	10
Weight Per each	0.264

### Uses, Certifications, and Standards

Mounting	Flanged Inlet
standard	UL 498