Pass and Seymour
30A NEMA L1530 Single Receptacle
Part No. L1530R



Turnlok® Single Receptacle 4-Wire 30A 3-Phase 250V

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007153057	Country Of Origin	Mexico
Number of Receptacles	1	Features	Brass Mounting Strap, Impact Resistant
Outlet Type	Locking	Application Sector	Industrial
Wall Plate Included	No	Standard	UL 498, FEDSPEC
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.61 in	Product Depth US	1.28 in

Product Height US	2.42 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes

Additional Information

Product Environmental Profile	Yes

Technical Information

Connection Location	Back and Side	Number of Wires	4
Amperage	30 A	Number of Poles	3-Way
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	L15-30R	Wire Connection Type	Screw Terminals
Voltage	250.0 V		