



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L15T848G840SG2 15W Led T8 48" 40K BLSTD Glass 2200LM

Keystone Technologies

Catalog Number	L15T848G840SG2
Manufacturer	Keystone Technologies
Description	15W Led T8 Lamp, 4, 4000K. Smartdrive. Glass Construction. Designed For Use With Instant Start Ballasts Only.
Weight per unit	0.6600 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	Ballast Dependent
ip rating	N/A
lumens	2200
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	15
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Construction	N/A
Description	15W LED T8 48" 40K BLSTD GLASS 2200LM
extra long description	Key KT-LED15T8-48G-840-S /G2-CP 15W
Long Description	15W LED T8 LAMP, 4, 4000K. SMARTDRIVE. GLASS CONSTRUCTION. DESIGNED FOR USE WITH INSTANT START BALLASTS ONLY.
Product Type	15W, 2200 Lumen, 4', 220' Beam Angle, Ballast Compatible, DL

Manufacturer Information

Brand	Keystone
GTIN	00890949020333
Manufacturers Part Number	KT-LED15T8-48G-840-S /G2-CP
UPC	890949020333



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	------------------------------------------------------------------

Packaging

Carton	25
--------	----

Weight Per each	0.66
-----------------	------

Uses, Certifications, and Standards

Energy Star	Y
-------------	---