

# Specifications

## Eaton L1630PW

Eaton Arrow Hart watertight locking plug, #18-10 AWG, 30A, Industrial, 480V, Back, Yellow, Steel, Watertight, L16-30, Three-pole, Four-wire, Santoprene, 0.43 to 1.15 in, IP67



### General specifications

<b>PRODUCT NAME</b>	Eaton Arrow Hart watertight locking plug
<b>CATALOG NUMBER</b>	L1630PW
<b>UPC</b>	040893642123
<b>PRODUCT LENGTH/DEPTH</b>	6.75 in
<b>PRODUCT HEIGHT</b>	4 in
<b>PRODUCT WIDTH</b>	4.25 in
<b>PRODUCT WEIGHT</b>	0.81 lb
<b>COMPLIANCES</b>	RoHS Compliant
<b>PRODUCT TYPE</b>	Watertight locking plug



Powering Business Worldwide

## Electrical Ratings

AMPERAGE RATING	30A
DEGREE OF PROTECTION	IP67
NEMA CONFIGURATION	L16-30
NUMBER OF POLES	Three-pole
NUMBER OF WIRES	4
TORQUE RATING	20 lbf-inch
VOLTAGE RATING	480 V

## Installation Specifications

ALLOWABLE WIRE SIZE	#18-10 AWG
WIRING METHOD	Back

## Product Specifications

APPLICATION	Industrial
CORD DIAMETER	0.43-1.15 in
MATERIAL	Santoprene
SPECIAL FEATURES	Watertight locking plug

## Environmental Specifications

ENVIRONMENTAL RESISTANCE	Watertight
--------------------------	------------

## Material Specifications

COLOR	Yellow
CONTACT MATERIAL	Steel

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - L1630PW</a> <a href="#">Arrow Hart watertight locking plugs, connectors and receptacles spec sheet</a>
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton L1630PW

Eaton Arrow Hart watertight locking plug, #18-10 AWG, 30A, Industrial, 480V, Back, Yellow, Steel, Watertight, L16-30, Three-pole, Four-wire, Santoprene, 0.43 to 1.15 in, IP67



### General specifications

<b>PRODUCT NAME</b>	Eaton Arrow Hart watertight locking plug
<b>CATALOG NUMBER</b>	L1630PW
<b>UPC</b>	040893642123
<b>PRODUCT LENGTH/DEPTH</b>	6.75 in
<b>PRODUCT HEIGHT</b>	4 in
<b>PRODUCT WIDTH</b>	4.25 in
<b>PRODUCT WEIGHT</b>	0.81 lb
<b>COMPLIANCES</b>	RoHS Compliant
<b>PRODUCT TYPE</b>	Watertight locking plug



Powering Business Worldwide

## Electrical Ratings

AMPERAGE RATING	30A
DEGREE OF PROTECTION	IP67
NEMA CONFIGURATION	L16-30
NUMBER OF POLES	Three-pole
NUMBER OF WIRES	4
TORQUE RATING	20 lbf-inch
VOLTAGE RATING	480 V

## Installation Specifications

ALLOWABLE WIRE SIZE	#18-10 AWG
WIRING METHOD	Back

## Product Specifications

APPLICATION	Industrial
CORD DIAMETER	0.43-1.15 in
MATERIAL	Santoprene
SPECIAL FEATURES	Watertight locking plug

## Environmental Specifications

ENVIRONMENTAL RESISTANCE	Watertight
--------------------------	------------

## Material Specifications

COLOR	Yellow
CONTACT MATERIAL	Steel

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - L1630PW</a> <a href="#">Arrow Hart watertight locking plugs, connectors and receptacles spec sheet</a>
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

