



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **L18.5T848GC840DX 18.5W Led T8 48" 40K Line DBL/SNGL Ended GC 2600LM** *Keystone Technologies*

Catalog Number	L18.5T848GC840DX
Manufacturer	Keystone Technologies
Description	18.5W Led T8 Tube, Glass Construction, 4FT, 4000K, 120-277V Input, 25 PCS Carton, Direct Drive Single or Double Ended. Gen.2
Weight per unit	0.6600 (lbs/each)
Product Category	20180918161041

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	2600
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Warranty	5
Wattage	18.5
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

### Descriptions

Construction	Frosted Shatterproof Glass
Description	18.5W LED T8 48" 40K LINE DBL/SNGL ENDED GC 2600LM
extra long description	Key KT-LED18.5T8-48GC-840-DX2 /G2-C
Long Description	18.5W LED T8 Tube, Glass Construction, 4ft, 4000K, 120-277V Input, 25 pcs Carton, Direct Drive Single or Double Ended. Gen.2
Product Type	18.5W, 2600 Lumen, 4' 240' Beam Angle, Ballast Bypass, DLC 4



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00843654120959
Manufacturers Part Number	KT-LED18.5T8-48GC-840-DX2 /G2-
UPC	843654120959

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	25
Weight Per each	0.66

## Uses, Certifications, and Standards

Energy Star	N
-------------	---